



seasunaquarium.com

SeaSun aquarium



[Aquarium Product](#)



[Salt Mixed \(Freshwater & Saltwater\)](#)




[Salinity Tester](#)



[PetLife \(Tester\) ReefLifeElite RHS Refractometer RHS-10 LED \(Range 0-100 ppt\)](#)

[PetLife \(Tester\) ReefLifeElite RHS Refractometer RHS-10 \(Range 0-100 ppt\) PetLife \(Treatment\) M1 10ml](#)



Brand: ([PetLife](#))
 Product Name: PetLife (Tester)
 ReefLifeElite RHS Refractometer
 RHS-10 LED (Range 0-100 ppt)
 SKU: PetLife ReefLifeElite
 Refractometer RHS10 LED (Res 1
 ppt)
 Barcode Link: **Price: à,¿ 1,800.00**

[Ask a question about this product](#)

853
 0 PetLife
 (Tester) ReefLifeElite RHS
 Refractometer RHS-10 LED
 (Range 0-100 ppt) 0

Benefit :

The ReefLifeElite[®] RHS Refractometer™ series (Refractometer Hand-Held Series) are designed for testing the concentration of salt water and brine. Its triple scale provides a direct reading of the specific gravity and concentration ppt (Parts per Thousand) of salt in water and the RHS proves itself valuable for agriculture food processing and wildlife management. This instrument is equipped with ATC (Automatic Temperature Compensation) system making it ideal for field use. Which model is to be chosen according to the concentration in the liquids and the parameter of refractometer.

ReefLifeElite[®] RHS Refractometer™ RHS04 is the narrow range.

ReefLifeElite[®] RHS Refractometer™ RHS10 is the wide range.

ReefLifeElite[®] RHS Refractometer™ RHS10 LED same **RHS10** but more contrast, and can use at dark area.

ReefLifeElite[®] RHS Refractometer™ Platinum RHS10 LED is the high quality material , high contrast, High accuracy, and can use at dark area.

Material :

Aluminium, Rubber and Quartz glass.

Directions :

Using soft cloth to clean the prism and testing prism, take a few drops of solution, put it on the prism, close the cover plate, escape from bubbles, to make the solution over the surface of prism.

Put the instrument into the version of alignment or light department, eyes can observed the field through Eyepiece. Rotate eyepiece to adjust hand wheel. To make the field of view of blue and white points clear. The scale of demarcation line is the density of solution.

Remark :

Keep out of reach of children.

Recommend product boosting effective :

ReefLifeElite[®] SaltBuffer 30 Solution™



ReefLifeElite[®] RHS Refractometer[™]

Number pieces in packaging:1 Number pieces in box:25
Customer Reviews: There are yet no reviews for this product.
Please log in to write a review.

You may also be interested in this/these product(s)
[Vendor Information](#)

